

# HYDROPHOBIC RIGID CANISTERS


## Canister Lid Features



Attached port caps eliminate cap loss and allow quick, secure capping.

Vacuum port provides optimum flow rate and easy hookup.

Translucent right angle connectors allow quick hookup, prevent kinked tubing and allow for visual inspection.



Large pour spout allows easy emptying and provides an adaptor port for the specimen collection accessory.

Tandem port for multiple canister connections.






Stepped patient port on Vac-U-Port, Hi-Flow and Quick-Fit lids allows direct patient tubing connection.

Self-sealing lid provides a leak-free seal when vacuum is applied.

Large patient port ensures greater suction for maximum site clearance.

Hydrophobic 800cc canister lid features self-sealing lid, pour spout with attached cap, vacuum port and patient port. Right angle connectors are not required.

**HYDROPHOBIC RIGID CANISTERS** provide superior protection and maximum performance.

DESCRIPTION	CATALOG NO.	PACKAGING	HYDROPHOBIC SHUT-OFF FILTER
 <p><b>800cc Hydrophobic Canister</b> with hydrophobic shutoff filter, built-in critical measure</p>	424410	100/case	 <p>Hydrophobic filter provides final filtration and overflow protection.</p> <p>Breathing screen separates filter stages for improved suction.</p> <p>Prefilter protects hydrophobic filter from erroneous shutoff.</p> <p>Tapered protective housing guards shutoff filter from splash or foam.</p>
 <p><b>1200cc Hydrophobic Canister</b> with hydrophobic shutoff filter</p>	434410	48/case	
 <p><b>1200cc Hydrophobic Canister</b> with 18" (46cm) and 6' (2m) connecting tubes</p>	438410	48/case	
 <p><b>2000cc Hydrophobic Canister</b> with hydrophobic shutoff filter</p>	435410	48/case	